

SICCO Desiccant, Bohlender

Dehumidifies the air inside a desiccator. Do not raise the silica gel for more than approx. 10 mm in the tray. 500 g of the desiccant can absorb up to 16 g humidity in 24 hours. Can be regenerated at 90 to 110°C in an oven. Must be stored in a dry, closed and hermetically sealed jar.

Silica gel with colour indicator from orange to dark brown and black (does not contain cobalt-II-chloride). Grain size 2.0 to 5.0 mm, loss after drying $\leq 4\%$.

Type	Weight g	Order No.
Bottle	360	10 17 69504
Bottle	720	10 17 69508
Canister	8000	10 17 69512

